Safety Signs en 150 7010, GHS/CLP





P003 P004 No open flame; Fire, open ignition source



P010



P020 Do not use lift in the event of fire



P028 Do not wear gloves



No thoroughfare



P011





P029

No photography





P030 Do not tie knots in rope

P005

Not drinking water

P012



P013

No activated

P006

No access for forklift

Do not walk or stand here



No children allowed





P008 No metallic articles



P001*

General prohibition sign

P007

No access for people

with active implanted

P025

Do not use this

Hot works

F003

P016 P018



P027 lift for people

Access prohibited

F004

Collection of fire-fighting equipment



Warning



W004 Warning Laser beam



W011 Warning





W019 W018 Warning Crushing Warning Automatic



Warning Oxidizing substance



W006

Warning Magnetic

W014

Warning Forklift

trucks and other

W021

Warning Risk of fire/

M001*

M007

Wear opaque

eve protection

M013

Wear face shield





W009 Warning

W007

Warning Floor

level obstacle

W015

Warning

Overhead load

W022

Warning Sharp

W037

Warning Run over

by remote operator

M002

instruction manual/hooklet

M008

Wear safety

footwear

M014



Biological hazard





W016



W017 Warning Toxic material Warning Hot surface





Warning Counter

rotating rollers

W023 Warning

Corrosive substance



W038 Warning

M009

Wear protective gloves

M015

Wear high visibility



M004

Wear protective

M016

Fire **Equipment**



F005



F012 **Fixed fire** extinguisher installation



Emergency

and First Aid



F006

Fire emergency

telephone

Fixed fire



extinguishing battery



E008

E014

Child seat presence

and orientation

F014 Remote release



F009 Wheeled fire



F015 Fire monitor

E001 Emergency exit

E009

Doctor

=

E015

Drinking water



A90* **

Direction arrow 90

Emergency exit

E010

heart defibrillator

F016

Emergency window



A45* ** Direction arrow 45°

E003

E011

Water fog





M005 Connect an earth

W027

Warning Optical



terminal to the ground



Wash your hands

M017

protection

M026 Use protective apron





M018

M027

Check guard





M028 Keep locked



GHS04

Compressed Gas



M032 M047 Wear anti-static Use self-contained breathing appliance footwear



M021 Disconnect before Use this walkway









E012







E059

Escape ladder



E007

E013

Stretcher

Evacuation



F024

Evacuation

temporary refuge



A90* **

Direction arrow 90



A45* **

Direction arrow 45°

safe condition

Rescue window

F029 **Emergency escape** breathing device



GHS07

GHS/CLP Signs







GHS08 Respiratory



GHS09

Environment



GHS05 **Hazard Corrosive** Acute



* Symbol can only be used with a legend. ** Sign is not part of the EN ISO 7010

The list of pictograms is not exhaustive, visit www.bradyeurope.com to find all available pictograms

