

J.T.Baker® Robotic Consumables

01. ROBOTIC TIPS,
PLATES & MORE


02. DESIGNED FOR
LESS DOWNTIME

03. ISO CERTIFIED
MANUFACTURING



J.T.Baker® Robotic Tips

Discover how our high quality J.T.Baker® products for third party robotic sampling systems can help improve your analytical and high throughput operations.



The quality you want for the trusted results you need.

J.T.Baker® premium conductive and clear tips for laboratory robotic and liquid handling systems, are manufactured and tested to deliver the reliable results you need to move science forward.

OVER A CENTURY OF QUALITY

For more than a century, customers around the world have trusted the application-optimized and function-tested performance of J.T.Baker® brand premium products to meet the demanding needs of a wide range of research and manufacturing applications. J.T.Baker® products are compatible with several leading robotic instruments on the market. The names and manufacturers of these products are mentioned below purely for identification purposes.

DESIGNED FOR LESS DOWNTIME

Leveraging decades of experience and innovation from our Germany-based production team, J.T.Baker® robotic tips help maximize robotic tool utilization and minimize downtime, with a straighter tip and lower coefficient of variation that reduces tip breakage.

ISO CERTIFIED MANUFACTURING

ISO certified quality: Our production facility is certified according to ISO 9001; we are certified according to ISO 13485:2016 for the production of medical and IVD products, and our manufacturing process adheres to the ISO 50001:2018 energy management system standard.

INDEPENDENTLY TESTED FOR PURITY

Each batch of blistered tips are tested according to rigorous quality procedures to ensure they are contaminant-free, and they are independently tested and certified free from DNase, RNase, PCR inhibitors and pyrogens.

PRECISE RESULTS. LESS DOWNTIME.

Engineered at the highest production standards, our J.T.Baker® robotic tips can dose even small volumes with high precision and no contamination. These tips are designed for some of the most popular robotic research workstations.

Suitable for a wide range of applications, J.T.Baker® conductive and clear tips are trusted by many life sciences and diagnostic laboratories worldwide and are supported for easy, convenient global ordering and delivery through Avantor's market leading e-commerce channel, **vwr.com**.

COMPLETE CLEANROOM AUTOMATION

J.T.Baker® robotic tips are literally untouched by human hands until you open the packaging: Our fully automated production line operates under cleanroom conditions to deliver tips that satisfy the most rigorous specifications for compatibility and cleanliness. And our tool making facilities and cutting-edge manufacturing technology result in some of the highest precision tips on the market.

All third-party trademarks referenced herein are the exclusive property of their respective owners.




Table of contents



TIPS

- J.T.Baker® tips type HT
Page 6
- J.T.Baker tips type HT 2
Page 7
- J.T.Baker® tips type TE
Pages 8 - 10
- J.T.Baker® tips type MP
Page 11
- J.T.Baker® tips type ST
Page 12
- J.T.Baker® tips type DX
Page 13
- J.T.Baker® tips type OLA
Page 14
- J.T.Baker® tips type QG
Page 15



PLATES

- PCR strip tubes & caps
Page 16
- PCR plate 96 rigid
Page 17
- SRW disposable plates
and tip combs
Pages 18 - 19
- Square well plates
Page 20
- Medio 96-well plates
Page 21
- 96-well plates
Page 22
- 384-well plates
Page 23
- Round well plates
and Microplate Lid
Page 24
- Dilution Strips SW
Page 25
- microTube rack
Page 26



Visit [vwr.com/precision-plastics](https://www.vwr.com/precision-plastics)
for more information.

J.T.Baker® tips type HT




J.T.Baker® tips suitable for third party robotic instruments Hamilton* Microlab Star*, Nimbus*, and other robotic instruments using the Hamilton's CO-RE* pipetting head.

With conductive robotic tips from Avantor, even small volumes can be dosed with high precision and without contamination. Conductivity enables the system to recognize the filling height and will provide a minimal immersion of the tip into the liquid, in order to ensure safe pipetting and dispensing.

Conductive tips are produced under cleanroom conditions and tested from independent laboratories to be free of DNA, DNase, RNase and PCR inhibitors. J.T.Baker tips HT are available with or without filter and in CE-IVD marked version for clinical diagnostic applications.



Single tray of 96 tips.

Volume	CE-IVD	Sterile	Filter	Conductive	Tip colour	Packed	Pk	Cat. No.
								
50 µl	No	No	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-0003
50 µl	Yes	No	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-2003
50 µl	No	No	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-0105
50 µl	Yes	No	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-2105
50 µl	No	Yes	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-1005
50 µl	Yes	Yes	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-3005
50 µl	No	Yes	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-1105
50 µl	Yes	Yes	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-3105
								
300 µl	No	No	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-0003
300 µl	Yes	No	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-2003
300 µl	No	No	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-0105
300 µl	Yes	No	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-2105
300 µl	No	Yes	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-1105
300 µl	Yes	Yes	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-3105
								
1000 µl	No	No	No	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-0005
1000 µl	Yes	No	No	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-2005
1000 µl	No	No	Yes	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-0105
1000 µl	Yes	No	Yes	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-2105
1000 µl	No	Yes	No	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-1005
1000 µl	Yes	Yes	No	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-3005
1000 µl	No	Yes	Yes	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-1105
1000 µl	Yes	Yes	Yes	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-3105

*Hamilton, Microlab Star™, Nimbus® and CO-RE® are registered trademarks of Hamilton company.


J.T.Baker® tips type HT 2

J.T.Baker® tips Suitable for use on third party robotic instruments Hamilton* Microlab Star* and Nimbus. Available in conductive version, with or without filter.




- Manufactured under cleanroom conditions (cleanroom Class 8)
- State-of-the-art quality control
- Ideal for high throughput analysis
- Barcoded trays for automated identification
- Packed in blister

J.T.Baker® robotic tips type HT 2 are suitable for third party robotic instruments Hamilton Microlab Star, Nimbus, and other robotic instruments using the Hamilton's CO-RE* or CO-RE* II pipetting head.

The validation of the tips on the instrument for specific applications is within the responsibility of the user.



J.T.Baker® tips type HT 2

Volume	CE-IVD	Sterile	Filter	Conductive	Tip colour	Packed	Pk	Cat. No.
								
50 µl	No	No	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-0015
50 µl	No	No	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-0115
50 µl	No	Yes	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-1015
50 µl	No	Yes	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49010-1115
								
300 µl	No	No	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-0015
300 µl	No	No	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-0115
300 µl	No	Yes	No	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-1015
300 µl	No	Yes	Yes	Yes	Black	12× 5 racks, 96 each, blistered	5.760	49008-1115
								
1000 µl	No	No	No	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-0015
1000 µl	No	No	Yes	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-0115
1000 µl	No	Yes	No	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-1015
1000 µl	No	Yes	Yes	Yes	Black	8× 5 racks, 96 each, blistered	3.840	49009-1115

*Hamilton, Microlab Star™, Nimbus® and CO-RE® are registered trademarks of Hamilton company.

J.T.Baker® tips type TE

J.T.Baker® tips suitable for third party robotic instruments Tecan* and other OEM workstations



J.T.Baker tips type TE are available in conductive and non-conductive version, with or without filter, and in CE-IVD marked version for clinical diagnostic applications.




The tips are manufactured under cleanroom conditions and are free of DNA, DNase, RNase and PCR inhibitors (blistered tips only).

In addition to the standard line, Avantor offers new wide bore robotic tips that have been developed with a 50% wider opening through which particularly viscous samples such as cell cultures, blood samples, macromolecules or oils can be pipetted gently and at high recovery rate.

J.T.Baker® tips type TE are suitable for use on Tecan* Freedom EVO, Tecan Fluent and other OEM robotic instruments using the same technology. They are available in S-Tray (hanging tray) or in C-Tray (refills for ANSI/SLAS format tip boxes).







C-TRAY, CONDUCTIVE, ANSI-SLAS RACK COMPATIBLE

Tip style	Volume	Sterile	CE-IVD	Filter	Tip colour	Colour code	Packed	Pk	Cat. No.
									
Standard	50 µl	-	-	-	Black	Yellow	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49006-0007
Standard	50 µl	-	+	-	Black	Yellow	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49006-2007
Standard	50 µl	-	-	+	Black	Yellow	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49006-0107
Standard	50 µl	-	+	+	Black	Yellow	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49006-2107
Standard	50 µl	+	-	+	Black	Yellow	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49006-1107
									
Standard	200 µl	-	-	-	Black	Blue	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49002-0007
Standard	200 µl	-	+	-	Black	Blue	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49002-2007
Standard	200 µl	-	-	+	Black	Blue	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49002-0107
Standard	200 µl	-	+	+	Black	Blue	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49002-2107
Standard	200 µl	+	-	+	Black	Blue	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49002-1107
Standard	350 µl	-	-	-	Black	Orange	16x5 nested refills, 96 each, 5 stack, C-Tray	7.680	49024-0008
									
Standard	1000 µl	-	-	-	Black	Red	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49003-0007
Standard	1000 µl	-	+	-	Black	Red	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49003-2007
Standard	1000 µl	-	-	+	Black	Red	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49003-0107
Standard	1000 µl	-	+	+	Black	Red	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49003-2107
Standard	1000 µl	+	-	+	Black	Red	Blistered, 12x2 refills, 96 each, single stack refill C-Tray	2.304	49003-1107






S-TRAY, CONDUCTIVE, HANGING TIPS

Tip style	Volume	Sterile	CE-IVD	Filter	Tip colour	Colour code	Packed	Pk	Cat. No.
									
Standard	50 µl	-	-	-	Black	Yellow	Cardboard, 18x10 refills, 96 each, hanging S-Tray	17.280	49006-0000
Standard	50 µl	-	+	-	Black	Yellow	Cardboard, 18x10 refills, 96 each, hanging S-Tray	17.280	49006-2000
Standard	50 µl	-	-	-	Black	Yellow	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49006-0006
Standard	50 µl	-	+	-	Black	Yellow	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49006-2006
Standard	50 µl	-	-	+	Black	Yellow	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49006-0106
Standard	50 µl	-	+	+	Black	Yellow	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49006-2106
Standard	50 µl	+	-	+	Black	Yellow	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49006-1106
Standard	50 µl	+	+	+	Black	Yellow	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49006-3106
									
Standard	200 µl	-	-	-	Black	Blue	Cardboard, 18x10 refills, 96 each, hanging S-Tray	17.280	49002-0000
Standard	200 µl	-	+	-	Black	Blue	Cardboard, 18x10 refills, 96 each, hanging S-Tray	17.280	49002-2000
Standard	200 µl	-	-	-	Black	Blue	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49002-0006
Standard	200 µl	-	+	-	Black	Blue	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49002-2006
Standard	200 µl	-	-	+	Black	Blue	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49002-0106
Standard	200 µl	-	+	+	Black	Blue	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49002-2106
Standard	200 µl	+	-	+	Black	Blue	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49002-1106
Standard	200 µl	+	+	+	Black	Blue	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49002-3106
									
Standard	1000 µl	-	-	-	Black	Red	Cardboard, 10x10 refills, 96 each, hanging S-Tray	9.600	49003-0000
Standard	1000 µl	-	+	-	Black	Red	Cardboard, 10x10 refills, 96 each, hanging S-Tray	9.600	49003-2000
Standard	1000 µl	-	-	-	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49003-0006
Standard	1000 µl	-	+	-	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49003-2006
Standard	1000 µl	-	-	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49003-0106
Standard	1000 µl	-	+	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49003-2106
Standard	1000 µl	+	-	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49003-1106
Standard	1000 µl	+	+	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49003-3106
									
Wide bore	1000 µl	-	-	-	Black	Red	Cardboard, 10x10 refills, 96 each, hanging S-Tray	9.600	49033-0000
Wide bore	1000 µl	-	+	-	Black	Red	Cardboard, 10x10 refills, 96 each, hanging S-Tray	9.600	49033-2000
Wide bore	1000 µl	-	-	-	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49033-0006
Wide bore	1000 µl	-	+	-	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49033-2006
Wide bore	1000 µl	-	-	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49033-0106
Wide bore	1000 µl	-	+	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49033-2106
Wide bore	1000 µl	+	-	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49033-1106
Wide bore	1000 µl	+	+	+	Black	Red	Blistered, 12x2 racks, 96 each, hanging S-Tray	2.304	49033-3106



S-TRAY, NON-CONDUCTIVE, HANGING TIPS

Tip style	Volume	Sterile	CE-IVD	Filter	Tip colour	Colour code	Packed	Pk	Cat. No.
									
Standard	50 µl	-	-	-	Clear	Yellow	Cardboard, 18x10 refills, 96 each, hanging S-Tray	17.280	49106-0000
Standard	50 µl	+	-	+	Clear	Yellow	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49106-1106
Standard	50 µl	+	+	+	Clear	Yellow	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49106-3106
									
Standard	200 µl	-	-	-	Clear	Blue	Cardboard, 18x10 refills, 96 each, hanging S-Tray	17.280	49102-0000
Standard	200 µl	-	-	-	Clear	Blue	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49102-0006
Standard	200 µl	+	-	+	Clear	Blue	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49102-1106
Standard	200 µl	+	+	+	Clear	Blue	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49102-3106
									
Standard	1000 µl	-	-	-	Clear	Red	Cardboard, 10x10 refills, 96 each, hanging S-Tray	9.600	49103-0000
Wide bore	1000 µl	-	-	-	Clear	Red	Cardboard, 10x10 refills, 96 each, hanging S-Tray	9.600	49133-0000
Standard	1000 µl	-	-	-	Clear	Red	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49103-0006
Standard	1000 µl	+	-	+	Clear	Red	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49103-1106
Standard	1000 µl	+	+	+	Clear	Red	Blistered, 12x2 refills, 96 each, hanging S-Tray	2.304	49103-3106

TIP BOX

Description	Pk	Cat. No.
Tip box for C-Tray 1000 µl tips	5	45009-2000
Tip box for C-Tray 50 and 200 µl tips	10	45009-3000



Conductive, 1000 µl, in tip box

*Tecan, Tecan Freedom Evo and Tecan Fluent are registered trademarks of Tecan company.

J.T.Baker® tips type MP

Available in conductive version, with filter, non-sterile, and in CE-IVD marked version for clinical diagnostic applications

- Manufactured under cleanroom conditions (cleanroom Class 8)
- State of the art quality control
- Barcoded trays for automated identification
- Free of DNA, DNase, RNase and PCR inhibitors
- Ideal for high throughput analysis
- Packed in blisters

The tips are suitable for use with Roche MagNA Pure* instruments.

The validation of the tips on the instrument for specific applications is within the responsibility of the user.



Volume	CE-IVD	Sterile	Filter	Conductive	Tip colour	Packed	Pk	Cat. No.
1000 µl	No	No	Yes	Yes	Black	8x 5 racks, 96 each, blistered	3.840	49209-0105
1000 µl	Yes	No	Yes	Yes	Black	8x 5 racks, 96 each, blistered	3.840	49209-2105


* Roche MagNA Pure® is a registered trademark of Roche company.



J.T.Baker® tips type ST

J.T.Baker® tips suitable for third party robotic instruments Stratec and other OEM workstations

Available in conductive version, with or without filter, and in CE-IVD marked version for clinical diagnostic applications. J.T.Baker® tips type ST are suitable for use on Euroimmun Analyzer and other robotic instruments using the same pipetting head.

The validation of the tips on the instrument for specific applications is within the responsibility of the user.



Volume	Sterile	CE-IVD	Filter	Tip colour	Packed	Pk	Cat. No.
							
300 µl	-	+	-	Black	18× 10 racks, 96 each, cardboard	17.280	49000-2000
300 µl	-	-	-	Black	18× 10 racks, 96 each, cardboard	17.280	49000-0000
300 µl	-	+	-	Black	12× 2 racks, 96 each, blistered	2.304	49000-2006
300 µl	-	-	-	Black	12× 2 racks, 96 each, blistered	2.304	49000-0006
300 µl	+	+	+	Black	12× 2 racks, 96 each, blistered	2.304	49000-3106
300 µl	+	-	+	Black	12× 2 racks, 96 each, blistered	2.304	49000-1106
							
1100 µl	-	+	-	Black	10× 10 racks, 96 each, cardboard	9.600	49001-2000
1100 µl	-	-	-	Black	10× 10 racks, 96 each, cardboard	9.600	49001-0000
1100 µl	-	+	+	Black	12× 2 racks, 96 each, blistered	2.304	49001-2106
1100 µl	-	-	+	Black	12× 2 racks, 96 each, blistered	2.304	49001-0106
1100 µl	+	+	+	Black	12× 2 racks, 96 each, blistered	2.304	49001-3106
1100 µl	+	-	+	Black	12× 2 racks, 96 each, blistered	2.304	49001-1106

J.T.Baker® tips type DX

J.T.Baker® tips suitable for use on third party robotic instruments Dynex*

J.T.Baker® tips suitable for use on Dynex* instruments. Available in non conductive version, without filter, in container rack, and in CE-IVD marked version for clinical diagnostic applications. With a modern production line and under cleanroom conditions, the tips are manufactured to provide the highest quality specifications for compatibility and cleanliness.

- For use with DSX* and DS2* instruments
- Packaging unit: 4x 108 tips
- Sample tips volume: 300 µl
- Reagent tips volume: 20 to 1300 µl



The validation of the tips on the instrument for specific applications is within the responsibility of the user.



Sample tips, blue.



Reagent tips, clear.

Volume	CE-IVD	Sterile	Filter	Conductive	Tip colour	Packed	Pk	Cat. No.
								
300 µl	No	No	No	No	Blue	1x 4 racks, 108 each	432	49136-0000
300 µl	Yes	No	No	No	Blue	1x 4 racks, 108 each	432	49136-2000
								
1300 µl	No	No	No	No	Clear	1x 4 racks, 108 each	432	49137-0000
1300 µl	Yes	No	No	No	Clear	1x 4 racks, 108 each	432	49137-2000

* Dynex, Dynex DSX and Dynex DS2 are registered trademarks of Dynex Technologies company.

J.T.Baker® tips type OLA

Robotic tips for efficient sample processing


Modern healthcare institutes require the highest standards from their partners. Avantor offers conductive tips that are suitable for use in OLA 2500 and AutoMate 1250/2550 instruments, in order to provide a smooth production flow and high quality results.

- Volume: 20 µl to 1200 µl
- Quantity per rack: 140 tips (sealed)
- Rigid rack for optimized tip acceptance in the OLA 2500 and AutoMate 1250/2550
- Packed: 8x 140 tips

The validation of the tips on the instrument for specific applications is within the responsibility of the user.



Conductive, 1200 µl, rack.

Volume	CE-IVD	Sterile	Filter	Conductive	Tip colour	Packed	Pk	Cat. No.
 1200 µl	No	No	No	Yes	Black	1× 8 racks, 140 each, foiled	1.120	49044-0000
1200 µl	No	No	Yes	Yes	Black	1× 8 racks, 140 each, foiled	1.120	49044-0100

J.T.Baker® tips type QG



J.T.Baker® tips suitable for use on third party robotic instruments QIAgility*

Type QG tips are available in conductive version, with filter, non-sterile, and in CE-IVD marked version for clinical diagnostic applications.

- Manufactured under cleanroom conditions (cleanroom class 8)
- State of the art quality control
- Free of DNA, DNase, RNase and PCR inhibitors
- Ideal for high-throughput analysis and DNA purification
- Packed in blister

The validation of the tips on the instrument for specific applications is within the responsibility of the user.



Volume	CE-IVD	Sterile	Filter	Conductive	Tip colour	Packed	Pk	Cat. No.
								
50 µl	No	No	Yes	Yes	Black	12× 2 racks, 96 each, blistered	2.304	49018-0106
50 µl	Yes	No	Yes	Yes	Black	12× 2 racks, 96 each, blistered	2.304	49018-2106
								
200 µl	No	No	Yes	Yes	Black	12× 2 racks, 96 each, blistered	2.304	49002-0106
200 µl	Yes	No	Yes	Yes	Black	12× 2 racks, 96 each, blistered	2.304	49002-2106

* QIAgility is a registered trademark of QIAGEN company.

J.T.Baker[®], PCR tubes and caps for qPCR, 8-Strips

PCR 8-tube strips and 8-cap strips are made of high-quality PP resin. Clear caps are compatible with qPCR application.

- Certified free from DNase, RNase and human DNA
- White 8-tube strips
- Corresponding 8-cap strips, clear to be ordered separately
- Ideal for low volume PCR and qPCR applications
- Low profile tubes help to reduce condensation
- Validated on Biorad CFX device

PCR strips and caps are manufactured under clean room conditions according to DIN EN ISO 14644-1:2016-06.

Description	Colour	Packed	Cat. No.
Tubes			
PCR strips 8-tubes without caps, low profile, 0,2 ml	White	120	43001-0033
Caps			
PCR strips 8-caps for qPCR	Clear	120	43001-0034



PCR strips 8-tubes without caps



PCR strips 8-caps for qPCR

PCR plate 96 rigid

Robotic PCR plate for PCR/qPCR set up

J.T.Baker® PCR plates are constructed with **2 components plastics**: Polycarbonate ultra-rigid frame for automation and Polypropylene ultra-thin wells for optimal thermal transfer and qPCR results.

The wells plastics exist in 2 colours (clear and white) for optimal qPCR results depending on the qPCR cyclers. White wells ensure high quality qPCR results by concentrating fluorescent signal, preventing loss of signal, and allowing for better signal detection by the instrument.

Available in barcoded and non-barcoded version, PCR plates are:

- Standard SBS format for use with automation
- Slightly raised well rims for better sealing
- Stackable and comes with 8 notches for easy insertion on thermoblock
- White or clear frame and wells
- Alphanumeric well markings
- V Bottom

Applications: Sample Preparation & PCR, qPCR, NGS library set up.

Certifications: Produced under cleanroom conditions (ISO 14644-1 Class 8). Free from DNA, DNase, RNase, and PCR inhibitors.

J.T.BAKER® PCR PLATE 96 RIGID


Description	Material	Frame colour	Well colour	No. of well	Profile	Skirt	Barcoded	Pk	Cat. No.
PCR plate, rigid, H1/H12/A12 cut corner	PP/PC	Clear	Clear	96	Low profile	Fully skirted	-	50	43001-0305
PCR plate, rigid, H1/H12/A12 cut corner	PP/PC	Clear	Clear	96	Low profile	Fully skirted	Yes	50	43001-0306
PCR plate, rigid, H1/H12/A12 cut corner	PP/PC	White	White	96	Low profile	Full skirted	-	50	43001-0301
PCR plate, rigid, H1/H12/A12 cut corner	PP/PC	White	White	96	Low profile	Full skirted	Yes	50	43001-0302

Packaging: 10 packs of 5 plates in PE foil.



SRW disposable plates and tip combs

For cleaning and mixing of samples.
For storage and preparation of substances.



- Newly developed cylindrical wells enable good bioturbation of samples
- Slightly raised rims reduce the risk of cross-contamination
- The alphanumeric code allows the registration and identification of individual samples even in confined spaces

SRW is in line with the SBS standard (Society for Biomolecular Screening). The plates and tip combs have been specifically developed for magnetic separation technology.

The technology is based on magnetic particles that allow fast and efficient sample preparation with high throughput. In order to perform this separation process in a reproducible way on a long-term basis, Avantor has developed precise plate components made from high purity polypropylene.

Suitable for:


- KingFisher™ 96 Flex and KingFisher™ Presto magnetic particle processor



SRW 0,2 ml



SRW 2,0 ml



SRW tip comb

J.T.BAKER® SRW DISPOSABLE PLATES AND TIP COMBS

Description	Well volume	Colour	Packed	Cat. No.
Plate SRW magnetic	0,2 ml	Transparent	60	43001-0506
Plate SRW magnetic	2,0 ml	Transparent	60	43001-0504
Tip Comb	-	Transparent	60	43001-0505

* KingFisher™ is a registered trademark of Thermo Fisher Scientific company.

Square well plates

For a maximum capacity utilization

Square well plates have been developed for optimal use of capacity when it comes to sample storage. Due to the SBS format, the outside dimensions of square well plates are given.

Form follows function: The construction of cavities is crucial for maximum absorption of liquids. Thin walled and parallel cavities ensure a maximum of contamination-free sample storage per well. Every square well plate has an alphanumeric marking. For closing square well plates, respective cap mats can be used as well as adhesive films. In addition, the plates can be closed by heat sealing. Analytical methods, as for example chromatography, can detect lowest impurities. For this reason, square well plates are manufactured out of pure polypropylene.

The relatively high volume allows closing of square well plates with cap mats without any liquid displacement and cross contamination, towards comparable plates with lower volumes from other manufacturers.




Square well plates 2 ml, 96 wells

- Total volume: Max. 2,5 ml/well
- Working volume: 50 µl up to 2,4 ml
- U-bottom shape
- Capmats need to be ordered separately



Square well plate 5 ml, 48 wells

- Total volume: Max. 5,0 ml/well
- Working volume: 50 µl up to 4,9 ml
- V-bottom shape
- Capmats need to be ordered separately



Square well plates 10 ml, 24 wells


- Total volume: Max. 10,0 ml/well
- Working volume: 50 µl up to 9,9 ml
- V-bottom shape
- Capmats need to be ordered separately




Description	Well volume	Colour	Packed	Cat. No.
24-well plate	10,0 ml	Transparent	20	43001-0066
48-well plate	5,0 ml	Transparent	20	43001-0062
96-well plate	2,0 ml	Transparent	20	43001-0020
Accessories				
Description	Optimal property	Material	Packed	Cat. No.
Capmat for J.T.Baker® Plate Square Well 48	Transparent	EVA	20	43001-0069
Capmat for J.T.Baker® Plate Square Well 24	Transparent	EVA	20	43001-0070
Capmat for J.T.Baker® Plate Square Well 96	Transparent	EVA	20	43001-0022

Medio 96-well plates

Saves 50% of storage capacity



Medio plates and plates RW, 2 ml more volume due to tangentially shared wells.



Medio plates 1 ml.

Medio plates

- Due to the tangency of Medio plates, up to 50% less stacking height is needed
- Higher well rims allow an airtight closure or sealing of Medio plates
- Alphanumeric marking allows the registration and identification of single samples
- Conical wells provide a good bioturbation

Medio plates 0,5 ml

- Height only: 20,5 mm
- Total volume: 0,65 ml/well
- Working volume: 20 µl to 500 µl/well

Medio plates 2,0 ml

- Height only: 44,0 mm
- Total volume: 2,0 ml/well
- Working volume: 1,9 ml/well

Medio plates 1 ml

- Height only: 27,0 mm
- Total volume: 1,2 ml/well
- Working volume: 50 µl to 1000 µl/well



J.T.BAKER® MEDIO 96-WELL PLATES


Description	Colour	Recommended working volume	Well volume	Packed	Cat. No.
Plate Medio, 0.5 ml	Transparent	20 - 500 µl	0,65 ml	40	43001-0102
Plate Medio, 1 ml	Transparent	50 - 1000 µl	1,2 ml	32	43001-0101
Plate Medio, 2 ml	Transparent	50 - 2000 µl	2,3 ml	20	43001-0103

96-well plates

Suitable for ELISA applications



The **96-well plates** are decoupled by intermediate wells. The mixing of samples by carry-over is reduced significantly with this shaping of the plate.



- 96-well plates are made out of highly transparent polystyrene that ensures an optimal surface for microscopic analysis
- 96-well plates are available in different shapes (U-, V- and F-shape)
- Due to the alphanumeric coding, samples can be clearly assigned and identified

J.T.BAKER® 96-WELL PLATES

Description	Packed	Cat. No.
96-well plate PP, U-bottom, 300 µl/well	64	43001-0600
96-well plate PS, U-bottom, 300 µl/well	100	43001-0117
96-well plate PS, V-bottom, 240 µl/well	100	43001-0118
96-well plate PS, F-bottom, 350 µl/well	100	43001-0119

384-well plates

Optimized for smaller volumes



- Available in PP for automated screening and storage systems
- Alphanumeric marking for sample identification
- Square wells for more volume
- V-bottom for high sample recovery
- 3 mm high frame for a stable, slip-free stacking
- Higher well rims avoid cross contamination

Description	Colour	Recommended working volume	Well volume	Packed	Cat. No.
PP plates	Transparent	5 - 110 µl	120 µl	60	43004-0120
PP plates	Transparent	5 - 180 µl	200 µl	40	43004-0200

Round well plates

Deepwell plate – standard in multifunction

- Raised wells of PP plus plates reduce the risk of cross-contamination and increase the security of heat sealing or sealing with adhesive films
- For defrosting of samples in a hot-water bath, PP plus plates have been developed
- U-shaped well bottom reduces death volume



Round wells plus with air escapes and raised rims.

Description	Colour	Well volume	Packed	Cat. No.
Round well PP plates raised rims plus	Transparent	1,0 ml	20	43001-0116
Round well PP plates raised rims	Transparent	1,0 ml	20	43001-0016
Round well PS plates raised rims	Clear	1,0 ml	20	43001-0010
Accessories				
Capmat for plate round well 1 ml			20	43001-0017

Microplate Lid

Polystyrene lid suitable for use with J.T.Baker® 384 and 96 SW.

- Material: Polystyrene
- Dimensions (outside): 129,2×86,0×9,0 mm



Microplate Lid, 96 well.

Description	Colour	Sterility	Packed	Cat. No.
PS lid for J.T.Baker® 384 and 96 well microplate	Clear	Non sterile	100	94001-0230

Plate, Dilution Strips SW

Deep well reservoir with eight wells.

- Strip of 8 wells
- Made of PP

J.T.Baker® dilution strips are suitable for use on third party robotic instruments Dynex DSX* and DS2*



Dilution Strips SW

Description	Packed	Working volume	Cat. No.
Dilution Strips SW	250	2 ml	43001 - 0031

* Dynex, Dynex DSX and Dynex DS2 are registered trademarks of Dynex Technologies company.

microTube rack


For safe sample storage



- microTube racks with 96 tubes of 1.2 ml in a format of 8 × 12 are compatible for robotic systems as well as for the individual sample storage. A special bottom plate allows easy handling of each sample, even in frozen condition
- The tubes are available as individual tubes or strips of 8 tubes of 1.2 ml. V-bottom reduces the dead volume. Can be closed for storage with 96-well cap mats or strips of 8 plug caps
- The rack is compatible with all current robotic systems with its footprint, in accordance to the SBS standard. A removable bottom plate fixes and centers the tubes and is ideal for storage. The alphanumeric marked rack can be refilled with individual tubes or strips of 8 tubes
- The stackable, transparent SBS format cover with alphanumeric marking on the lid snaps into position to close with the rack

MICROTUBE RACK

Description	Well volume	Packed	Cat. No.
Microtube rack 96 individual tubes	1.2 ml	10	45000-0000
Micro tube rack 8 stripes	1.2 ml	10	45005-0000
Individual tubes	1.2 ml	960	45003-0000
Strip of 8 tubes	1.2 ml	120	45000-0008
Accessories			
Capmat for J.T.Baker® plate 1 ml	1 ml	20	43001-0017
Strip of 8 plug caps	Diam. 7 mm	120	45000-0006



SCIENCE *DELIVERED*

From scientific discovery to scale-up and commercial delivery, you need mission-critical products, services and solutions on a global scale.

Avantor® offers global access to our own portfolio of trusted, quality brands and critical products through our premier delivery platform, VWR®. All of this, combined with infrastructure strategically located to help serve your specific needs, helps move science forward – fast. That's **science delivered**.

Get the mission-critical scientific products and solutions you need from Avantor, delivered through VWR.

➔ vwr.com/science-delivered

 **avantor**™
delivered by **VWR**™

AUSTRIA

VWR International GmbH
Graumannsgasse 7
1150 Wien
Tel.: +43 1 97 002 0
info.at@vwr.com

BELGIUM

VWR International bv
Researchpark Haasrode 2020
Geldenaaksebaan 464
3001 Leuven
Tel.: +32 (0) 16 385 011
vwr.be@vwr.com

CZECH REPUBLIC

VWR International s. r. o.
Veetee Business Park
Pražská 442
CZ - 281 67 Stříbrná Skalice
Tel.: +420 321 570 321
info.cz@vwr.com

DENMARK

VWR International A/S
Tobaksvej 21
2860 Søborg
Tel.: +45 43 86 87 88
info.dk@vwr.com

FINLAND

VWR International Oy
Valimotie 17-19
00380 Helsinki
Tel.: +358 (0) 9 80 45 51
info.fi@vwr.com

FRANCE

VWR International S.A.S.
Immeuble Estréo
1-3 rue d'Aurion
93114 Rosny-sous-Bois cedex
Tel.: 0 825 02 30 30* (national)
Tel.: +33 (0) 1 45 14 85 00
(international)
info.fr@vwr.com
* 0,18 € TTC/min + prix appel

GERMANY

VWR International GmbH
Hilpertstraße 20a
D - 64295 Darmstadt
Tel.: 0800 702 00 07* (national)
Tel.: +49 (0) 6151 3972 0
(international)
info.de@vwr.com
*Freecall

HUNGARY

VWR International Kft.
Simon László u. 4.
4034 Debrecen
Tel.: +36 52 521130
info.hu@vwr.com

IRELAND

VWR International Ltd
Orion Business Campus
Northwest Business Park
Ballycoolin
Dublin 15
Tel.: +353 (0) 1 88 22 222
sales.ie@vwr.com

ITALY

VWR International S.r.l.
Via San Giusto 85
20153 Milano (MI)
Tel.: +39 02 3320311
info.it@vwr.com

THE NETHERLANDS

VWR International B.V.
Postbus 8198
1005 AD Amsterdam
Tel.: +31 (0) 20 4808 400
info.nl@vwr.com

NORWAY

VWR International AS
Brynsalleen 4,
0667 Oslo
Tel.: +47 22 90 00 00
info.no@vwr.com

POLAND

VWR International Sp. z o.o.
Limbowa 5
80-175 Gdansk
Tel.: +48 58 32 38 200
info.pl@vwr.com

PORTUGAL

VWR International –
Mat. de Laboratório, Soc.
Unipessoal, Lda
Edifício Ramazzotti
Avenida do Forte 6, P-1.09 e
P-1.10
2790-072 Carnaxide
Tel.: +351 21 3600 770
Info.pt@vwr.com

SPAIN

VWR International Eurolab S.L.U.
C/ Tecnología 5-17
A-7 Llinars Park
08450 - Llinars del Vallès
Barcelona
Tel.: +34 902 222 897
info.es@vwr.com

SWEDEN

VWR International AB
Fagerstagatan 18b
163 94 Stockholm
Tel.: +46 (0) 8 621 34 20
kundservice.se@vwr.com

SWITZERLAND

VWR International GmbH
Lerzenstrasse 16/18
8953 Dietikon
Tel.: +41 (0) 44 745 13 13
info.ch@vwr.com

UK

VWR International Ltd
Customer Service Centre
Hunter Boulevard - Magna Park
Lutterworth
Leicestershire
LE17 4XN
Tel.: +44 (0) 800 22 33 44
uksales@vwr.com

CHINA

VWR (Shanghai) Co., Ltd
Bld.No.1, No.3728 Jinke Rd,
Pudong New District
Shanghai, 201203- China
Tel.: 400 821 8006
info_china@vwr.com

INDIA

VWR Lab Products Private Limited
No.139. BDA Industrial Suburb,
6th Main, Tumkur Road, Peenya Post,
Bangalore, India – 560058
Tel.: +91 80 28078400
vwr_india@vwr.com

KOREA

Avantor Performance Materials Korea Ltd
2F ACE Gwanggyo Tower I, Daehak 4ro 17
Yeongtong-gu Suwon, Korea 16226
Tel.: +82 31 645 7256
saleskorea@avantorsciences.com

MIDDLE EAST & AFRICA

VWR International FZ-LLC
Office 203, DSP Lab Complex,
Dubai Science Park,
Dubai, United Arab Emirates
Tel.: +971 4 5573271
Info.mea@vwr.com

SINGAPORE

VWR Singapore Pte Ltd
The Metropolis
Tower 1, #05-03
9 North Buona Vista Drive
Singapore 138588
Tel.: +65 6505 0760
sales.sg@vwr.com

GO TO **VWR.COM** FOR THE LATEST NEWS, SPECIAL OFFERS AND DETAILS FROM YOUR LOCAL VWR SUPPORT TEAM

Prices, product, and/or services details are current when published and subject to change without notice. | Certain products or services may be limited by country, federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or affiliates. Offers valid in countries listed above, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its affiliates, unless otherwise noted. | Visit vwr.com to view our privacy policy, trademark owners, and additional disclaimers. © 2023 Avantor, Inc. All rights reserved.